



## Pneumatic shut-off screwdriver, Type: S2416L



### Order data

Order number	079165 S2416L
GTIN	7322590017040
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal  $\varnothing$ .

- **Precise, non-wearing cut-out clutch.**
- **High torque accuracy.**

Particularly suitable for series production screwdriving with quick-release bit holder for E 6.3 bits (see No. 674200 ff).

Oil-free - no additional pneumatic oiler required.

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

recommended hose size (internal $\varnothing$ )	10 mm
maximum air consumption	360 l/min
Manufacturer's designation	S2416L
Tool arbor size	1/4 in
Torque range	0.5 - 1.6 Nm
maximum screw $\varnothing$ (8.8 - 12.9)	M3
Weight	0.9 kg

maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Format	Rod
Operating noise	73 dB(A)
maximum speed	1500 min <sup>-1</sup>
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver