

**DYMO**
**Labelling machine, Type: LM360D**

**Order data**

Order number	085500 LM360D
GTIN	3501170879528
Item class	08U

**Description**
**Version:**

**Robust portable** labelling machines for fast and simple production of self-adhesive plastic labels. Permanent thermal transfer printing. Adjustable tape advance and reverse. Power supply from rechargeable **Li-ion battery**, mains charger. Simple text generation with quick-access buttons.

**Application:**

The labels stick to nearly all smooth grease-free surfaces.

**Supplied with:**

Includes lettering tape black on white and user instructions.

**Note:**

- **Different language versions can be installed.**
- **With German QWERTZ keyboard ex stock, French AZERTY keyboard available on a short lead time.**

**Technical description**

suitable tape cartridge	D1
Tape cut-off type	manual
Number of lettering styles	7
maximum character height	14.9 mm

Type	LM360D
Number of font sizes	7
Length	150 mm
Number of text lines	2
Number of font widths	3
Number of visible characters in the display	2×14
Mains adaptor	Including
Width	197 mm
Print colour	black
Keyboard layout	QWERTZ
Number of available characters/symbols	221
available tape widths	6; 9; 12; 19 mm
Weight including rechargeable battery	621 g
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Height	71 mm
Power supply	Rechargeable battery-powered
Manufacturer's designation	Dymo 360D
Type of product	Labelling machine

## Accessories

Printer ribbon cartridge 6 mm×7 m polyester Type W	085530 W
Printer ribbon cartridge 12 mm×7 m polyester Type Y	085520 Y
Printer ribbon cartridge 12 mm×7 m polyester Type T	085520 T
Printer ribbon cartridge 24 mm×7 m polyester Type Y	085560 Y
Printer ribbon cartridge 24 mm×7 m polyester Type R	085560 R
Printer ribbon cartridge 19 mm×7 m polyester Type W	085550 W
Printer ribbon cartridge 12 mm×7 m polyester Type R	085520 R

Printer ribbon cartridge 19 mm×7 m polyester Type T	085550 T
Printer ribbon cartridge 12 mm×7 m polyester Type W	085520 W
Printer ribbon cartridge 19 mm×3.5 m nylon Type W	085516 W
Printer ribbon cartridge 19 mm×7 m polyester Type R	085550 R
Printer ribbon cartridge 24 mm×7 m polyester Type W	085560 W
Printer ribbon cartridge 9 mm×7 m polyester Type W	085540 W
Printer ribbon cartridge 9 mm×7 m polyester Type Y	085540 Y
Printer ribbon cartridge 19 mm×7 m polyester Type Y	085550 Y