

DYMO
Labelling machine, Type: LM420P

Order data

Order number	085500 LM420P
GTIN	3501170915448
Item class	08U

Description
Version:

Robust portable labelling machines for fast and simple production of self-adhesive plastic labels. Permanent thermal transfer printing. Adjustable tape advance and reverse. Power supply from rechargeable **Li-ion battery**, mains charger. Simple text generation with quick-access buttons. Slim-line printer with **ABC keyboard** and large 4-line display with background lighting and print preview. USB port.

Application:

The labels stick to nearly all smooth grease-free surfaces.

Supplied with:

Includes lettering tape black on white and user instructions.

Note:

- **Different language versions can be installed.**
- **With German QWERTZ keyboard ex stock, French AZERTY keyboard available on a short lead time.**

Technical description

Number of visible characters in the display	4×30
Number of text lines	1 – 4

Tape cut-off type	manual
maximum character height	14.9 mm
Width	104 mm
Number of available characters/symbols	325
Number of font widths	8
Length	215 mm
suitable tape cartridge	D1
available tape widths	6; 9; 12; 19 mm
Type	LM420P
Mains adaptor	including
Number of font sizes	7
Print colour	black
Number of lettering styles	12
Keyboard layout	ABC
Special features	USB
Weight including rechargeable battery	415 g
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Height	57 mm
Power supply	Rechargeable battery-powered
Manufacturer's designation	420P
Type of product	Labelling machine

Accessories

Printer ribbon cartridge 12 mm×7 m polyester Type R	085520 R
Printer ribbon cartridge 24 mm×7 m polyester Type R	085560 R
Printer ribbon cartridge 12 mm×7 m polyester Type Y	085520 Y
Printer ribbon cartridge 9 mm×7 m polyester Type Y	085540 Y

Printer ribbon cartridge 19 mm×7 m polyester Type T	085550 T
Printer ribbon cartridge 24 mm×7 m polyester Type W	085560 W
Printer ribbon cartridge 19 mm×7 m polyester Type Y	085550 Y
Printer ribbon cartridge 24 mm×7 m polyester Type Y	085560 Y
Printer ribbon cartridge 19 mm×7 m polyester Type R	085550 R
Printer ribbon cartridge 12 mm×7 m polyester Type T	085520 T
Printer ribbon cartridge 12 mm×7 m polyester Type W	085520 W
Printer ribbon cartridge 19 mm×3.5 m nylon Type W	085516 W
Printer ribbon cartridge 6 mm×7 m polyester Type W	085530 W
Printer ribbon cartridge 9 mm×7 m polyester Type W	085540 W
Printer ribbon cartridge 19 mm×7 m polyester Type W	085550 W