



Pneumatic screwdriver, Type: S2326



Order data

Order number	079161 S2326
GTIN	7322590011406
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal \emptyset . Versatile application screwdrivers with 1/4 inch hexagon socket quick-release chuck for E 6.3 bits (see No. 674200 ff), reversible for **clockwise / anticlockwise** rotation.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Operating noise	83 dB(A)
Manufacturer's designation	S2326
Torque range	up to 4,5 Nm
maximum speed	2400 min ⁻¹
maximum air consumption	336 l/min
recommended hose size (internal \emptyset)	6.3 mm

maximum screw \varnothing (8.8 - 12.9)	M6
Weight	0.8 kg
Length	178 mm
maximum vibration to EN	$< 2.5 \text{ m/s}^2$
Compressed air connection	1/4 in
Connection thread	BSP
Bit socket	F 6.3
Type of product	Screwdriver