

DYMO**Labelling machine, Type: LM500TS****Order data**

Order number	085500 LM500TS
GTIN	3501170946459
Item class	08U

Description**Version:**

Robust portable labelling machines for fast and simple production of self-adhesive plastic labels. Permanent thermal transfer printing. Adjustable tape advance and reverse. Power supply from rechargeable **Li-ion battery**, mains charger. Simple text generation with quick-access buttons. **With full-colour touch screen**, also prints graphics, barcodes, and logos with 300 dpi resolution. Profiles for up to 5 users. **USB interface.**

Application:

The labels stick to nearly all smooth grease-free surfaces.

Supplied with:

Includes lettering tape black on white and user instructions. LabelManager 500TS labelling machine, battery pack Li-ion charging adapter, USB cable.

Note:

- **Different language versions can be installed.**
- **With German QWERTZ keyboard ex stock, French AZERTY keyboard available on a short lead time.**
- **Not available in all countries.**
- **Express delivery not possible.**

Technical description

Length	190 mm
Print colour	black
Number of text lines	1 – 5
available tape widths	6; 9; 12; 19; 24 mm
Number of font sizes	25
Keyboard layout	QWERTZ
Type	LM500TS
Number of available characters/symbols	325
maximum character height	22 mm
Number of font widths	2
Width	165 mm
Tape cut-off type	automatic
suitable tape cartridge	D1
Mains adaptor	including
Number of lettering styles	32
Special features	USB / barcode
Weight including rechargeable battery	800 g
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Height	95 mm
Power supply	Rechargeable battery-powered
Manufacturer's designation	Dymo 500 TS
Type of product	Labelling machine

Accessories

Printer ribbon cartridge 24 mm×7 m polyester Type Y	085560 Y
Printer ribbon cartridge 24 mm×7 m polyester Type R	085560 R
Mains adapter for No. 085500	085570

Printer ribbon cartridge 24 mm x 7 m polyester Type W

085560 W