



Pneumatic screwdriver, Type: S2305



Order data

Order number	079161 S2305
GTIN	7322590011390
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø. Versatile application screwdrivers with 1/4 inch hexagon socket quick-release chuck for E 6.3 bits (see No. 674200 ff), reversible for **clockwise / anticlockwise** rotation.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

maximum air consumption	336 l/min
Operating noise	83 dB(A)
Manufacturer's designation	S2305
recommended hose size (internal Ø)	6.3 mm
Torque range	up to 12 Nm
maximum speed	750 min ⁻¹

maximum vibration to EN	< 2.5 m/s ²
maximum screw Ø (8.8 - 12.9)	M8
Weight	0.9 kg
Length	198 mm
Compressed air connection	1/4 in
Connection thread	BSP
Bit socket	F 6.3
Type of product	Screwdriver