

**Pneumatic shut-off screwdriver, Type: S2450P****Order data**

Order number	079165 S2450P
GTIN	7322590017057
Item class	03R

**Description****Version:**

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.

- **Precise, non-wearing cut-out clutch.**
- **High torque accuracy.**

Particularly suitable for series production screwdriving with quick-release bit holder for E 6.3 bits (see No. 674200 ff).

Oil-free - no additional pneumatic oiler required.

**Spare part:**

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

**Technical description**

recommended hose size (internal Ø)	10 mm
Manufacturer's designation	S2450P
maximum vibration to EN	$< 2.5 \text{ m/s}^2$
maximum air consumption	360 l/min
Torque range	2.4 - 5 Nm
Format	Pistol

Weight	1.1 kg
Tool arbor size	1/4 in
maximum screw Ø (8.8 - 12.9)	M5
Operating noise	78 dB(A)
maximum speed	1100 min <sup>-1</sup>
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver