

**DYMO**
**Labelling machine, Type: 4200**

**Order data**

Order number	085500 4200
GTIN	3501170955970
Item class	08U

**Description**
**Version:**

**Robust portable** labelling machines for fast and simple production of self-adhesive plastic labels. Permanent thermal transfer printing. Adjustable tape advance and reverse. Power supply from rechargeable **Li-ion battery**, mains charger. Simple text generation with quick-access buttons. **Robust industrial label printer** for easy labelling of cables, control panels, shelves etc. **Direct access buttons** for frequently-used electro-technical symbols.

**Application:**

The labels stick to nearly all smooth grease-free surfaces.

**Supplied with:**

Includes lettering tape black on white and user instructions. **Without battery and mains adapter.**

**Note:**

- **Different language versions can be installed.**
- **With German QWERTZ keyboard ex stock, French AZERTY keyboard available on a short lead time.**

**Technical description**

Mains adaptor	accessories
---------------	-------------

Keyboard layout	QWERTZ
suitable tape cartridge	RHINO
Width	127 mm
Length	181 mm
Print colour	black
Number of font sizes	7
maximum character height	13 mm
Number of font widths	2
Tape cut-off type	manual
Type	Rhino 4200
available tape widths	6; 9; 12; 19 mm
Number of lettering styles	5
Number of visible characters in the display	11
Number of text lines	1 – 4
Number of available characters/symbols	50
Special features	Label storage
Weight including rechargeable battery	770 g
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Height	62 mm
Power supply	Rechargeable battery-powered
Manufacturer's designation	Rhino 4200
Type of product	Labelling machine

## Accessories

Printer ribbon cartridge 12 mm×3.5 m nylon Type W	085515 W
Printer ribbon cartridge 12 mm×5.5 m vinyl Type W	085517 W
Mains adapter for No. 085500	085570

