

Garant**Shelvingcabinet without door, Height: 2000mm****Order data**

Order number	945009 2000
GTIN	4062406331993
Item class	9GI

Description**Version:**

Shelf cabinet in 30×11G. Mountings for storage shelves at 25-mm intervals.

Colour:

Body RAL 7035 light grey.

Note:

See No. 944061, 944065 for storage shelves for GridLine racking cupboards.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width in G	30
Weight	45 kg
Width	750 mm
Cabinet fronts	open
Height	2000 mm

Electronic locking system can be retrofitted	no
Depth in G	11
Usable height	1845 mm
Depth	275 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Racking cupboard