



„speedE® II“ VDE set 1, Type: 1



Order data

Order number	667268 1
GTIN	4010995443184
Item class	60N

Description

Version:

Quicker working due to electronic screw tightening over 2 power levels: 0.4 Nm and 1.0 Nm. This opens up a new range of applications. A material protection function for both power levels is integrated, which switches off the screw tightening function after the tightening torque of 0.4 Nm or 1.0 Nm is reached. Further tightening by hand is possible without having to change grip, using the electronic ratchet. The manual strength of the user determines the maximum tightening torque. The integrated ring LED ensures optimum illumination of the screw during the screw fastening. Holder and bits **fully insulated to 1000 V to DIN EN 6000 / VDE 0682-201.**

Supplied with:

E-screwdriver handle speedE® II
 1× slimBit SL 0.6×3.5; bit length: 75 mm.
 1× PowerBit SL/PZ2; bit length: 75 mm.
 USB charger (without mains adapter).
 2 rechargeable Li-ion batteries.
 In a sturdy plastic box L-BOXX® Mini

Technical description

Standard	DIN EN IEC 60900 / VDE 0682-201
Storage in	Plastic case

Type of rechargeable battery	Lithium-ion
maximum tightening torque	1 Nm
Drive profile	Slot-head screwdriver
Drive profile	Combination profile screwdriver Pozidriv / slot-head
Number of pieces	7
Number of rechargeable batteries contained	2
Replaceable battery	yes
Battery voltage	4.2 V
Battery capacity	1.5 Ah
Power supply	Rechargeable battery-powered
Type of product	Screwdrivers