



## Cordless impact wrench / driver, Type: 71150864



### Order data

Order number	074000 71150864
GTIN	4014586891651
Item class	03F

### Description

#### Version:

Powerful cordless impact wrench with **brushless motor and torque adjustment in 6 steps**. Robust all-metal impact drive and ergonomic handling thanks to soft-grip coating.

- **3/4-inch square drive socket.**
- **1,050 Nm max. torque.**
- **with MultiVolt interface.**

#### Supplied with:

**Version without battery and without charger**, including L-BOXX. **Without battery and without charger**, with carrying case.

#### Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

### Technical description

Tool arbor drive profile	External square drive
Number of rechargeable batteries contained	0
maximum torque	1050 Nm

Type of rechargeable battery	Lithium-ion
maximum screw Ø (8.8 - 12.9)	M27
Packaging	Carrying case
suitable battery - supplier / battery type / voltage	Fein type E 12 V
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Number of impacts	0 - 2200 min <sup>-1</sup>
Battery voltage	12 V
Battery voltage	18 V
typical application	Heavy Duty
Manufacturer's designation	ASCD 18-1000
Tool arbor size	3/4 in
maximum vibration to EN	12.9 m/s <sup>2</sup>
Weight	3 kg
Power supply	Rechargeable battery-powered
Type of product	Impact wrench

## Accessories

Li-ion battery Rechargeable battery type, battery voltage FE12 V	073835 FE12
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
Li-ion battery Rechargeable battery type, battery voltage FE12 V	073837 FE12