



Beveller handheld, Type: KFH17-8R



Order data

Order number	078125 KFH17-8R
GTIN	4014586892696
Item class	03F

Description

Version:

For producing chamfers and radii on flat materials, sheet metal and containers, internal and external edges, contour profiles and for rounding off holes. General-purpose beveller with booster technology for optimum weld seam preparation and preparation for subsequent coatings. Non-fatiguing working with FEIN **ErgoGrip**. Beveller up to 8 mm.

Supplied with:

1 machine (without milling head, without guide roller, without indexable inserts), 3 clamping screws, 1 copper paste, 1 hexagon L-wrench 5 mm, 1 Torx screwdriver TX 15, 1 plastic tool case.

Note:

The necessary accessories can be found in our eShop from No. 078136 – 078138.

Technical description

Radius	3 mm
Weight	4.6 kg
Cable length	4 m
Power consumption	1700 W
Disc Ø	118 mm
Manufacturer's designation	KFH 17-8 R

Chamfer angle	30 degrees
Chamfer angle	45 degrees
No load speed	2300 - 7500 min ⁻¹
Power supply	Mains operated
Packaging	Carrying case
Type of product	Deburring and chamfering machine

Accessories

Beveller Type 6430100101	078137 6430100101
Insert screw setfor beveller Type 3135007500	078139 3135007500
Indexable insert set Type 6430200601	078138 6430200601
Guide roller Type 6430300401	078136 6430300401
Guide roller Type 6430300201	078136 6430300201
Indexable insert set Type 6430200401	078138 6430200401