

**LED cordless lamp 0 version without battery, 12.0 V, Type: M12SLED****Order data**

Order number	073210 M12SLED
--------------	----------------

GTIN	
------	--

Item class	07A
------------	-----

Description**Version:**

Robust Li-Ion battery lights with high light intensity. Hand-held lamp with 2 lighting levels.
Range of up to 650 metres.

LED hand-held floodlight, 12 volts, with **TRUEVIEW™ technology**.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Suitable for:

Milwaukee 12 V batteries MB12.

Supplied with:

Cordless lamp without battery and without charger.

Technical description

Power supply	Rechargeable battery-powered
--------------	------------------------------

Number of rechargeable batteries contained	0
--	---

Working life	8 h
IP Index of Protection	IP 54
ATEX zone	no
Manufacturer's designation	M12SLED-0
Illumination	750 lm
Type of rechargeable battery	Lithium-ion
Battery voltage	12 V
Illumination step 2	400 lm
Illumination range	650 m
Product name attribute	12.0 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Type of product	Work lamp

Accessories

Li-ion system M12B4 Battery type MB12	073815 MB12
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C
Battery starter set Type M12NRG4	073839 M12NRG4
Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
Battery charger Type M1218SC	073840 M1218SC
Li-ion system M12B6 Battery type MB12	073829 MB12