

## LED desk lamp, Type: 12



### Order data

Order number	928653 12
GTIN	7612176079730
Item class	97G

### Description

#### Version:

Energy-efficient LED desk lamp made from aluminium, with uniform, homogeneous, shadow-free and non-dazzling lighting. Can be dimmed using the control button in the lamp head in 5 levels, with memory function. With sturdy aluminium base, base Ø 180 mm. Colour temperature neutral white 4,000 K.

The lamp incorporates built-in LED bulbs.

The LED bulbs cannot be exchanged within the lamp.

Working duration: 20,000 hours.

Maximum height: 570 mm.

Maximum projection: 740 mm.

### Technical description

Light colour	neutral white
Lamp body height	22.5 mm
Number of LEDs	24
Power consumption	12 W

Lamp body length	425 mm
Bulb	LED lamp
Lamp replaceable	no
Lamp body width	46 mm
Power supply	Mains operated
Support arm reach	470 mm
Colour temperature	4000 K
On/Off switch	yes
Type of product	Desk lamp / workstation lamp