



## Slotted reducing adapter with cooling, Ø 20 mm, Clamping range Ø D1: 3mm



### Order data

Order number	302150 3
GTIN	4060576155234
Item class	33T

### Description

#### Version:

**Schunk** GZB-S reducing adapter.

Flexible length pre-setting possible through movable intermediate piece.

**With cooling channel slots.**

#### Application:

- **For drilling, reaming, milling, and tool sharpening.**
- **Very high flexibility due to reduction in clamping diameter.**
- **Very high torque guarantees a higher volume of metal removal compared to direct clamping.**
- **Concentricity  $\pm 5 \mu\text{m}$  (system accuracy at  $3 \times D$ ).**
- **Concentricity  $\pm 2 \mu\text{m}$  (for reducing adapter).**
- **Can be used in all commercially available hydraulic chucks.**

#### Suitable for:

Hydraulic chuck with **clamping  $\varnothing 20 \text{ mm}$** .

### Technical description

Overall length L	52.5 mm
Clamping $\varnothing D_1$	3 mm
$\varnothing D$	20 mm
Product name attribute	$\varnothing 20 \text{ mm}$
Concentricity system	5 $\mu\text{m}$

Type of product

Reducing adapter