



Slotted reducing adapter with cooling, Ø 20 mm, Clamping range Ø D1: 6mm



Order data

Order number	302150 6
GTIN	4060576155203
Item class	33T

Description

Version:

Schunk GZB-S reducing adapter.

Flexible length pre-setting possible through movable intermediate piece.

With cooling channel slots.

Application:

- **For drilling, reaming, milling, and tool sharpening.**
- **Very high flexibility due to reduction in clamping diameter.**
- **Very high torque guarantees a higher volume of metal removal compared to direct clamping.**
- **Concentricity $\pm 5 \mu\text{m}$ (system accuracy at $3 \times D$).**
- **Concentricity $\pm 2 \mu\text{m}$ (for reducing adapter).**
- **Can be used in all commercially available hydraulic chucks.**

Suitable for:

Hydraulic chuck with **clamping $\varnothing 20 \text{ mm}$** .

Technical description

Clamping $\varnothing D_1$	6 mm
Overall length L	52.5 mm
$\varnothing D$	20 mm
Product name attribute	$\varnothing 20 \text{ mm}$
Concentricity system	5 μm

Type of product

Reducing adapter