



Slotted reducing adapter sealed, Ø 20 mm, Clamping range Ø D1: 10mm



Order data

| | |
|--------------|---------------|
| Order number | 302165 10 |
| GTIN | 4060576159812 |
| Item class | 33T |

Description

Version:

Schunk GZB-S with seal.

Tight against coolant up to 80 bar.

Flexible length pre-setting possible through movable intermediate piece.

Sealed (rubber plug).

Application:

- **For drilling, reaming, milling, and tool sharpening.**
- **Very high flexibility due to reduction in clamping diameter.**
- **High torque guarantees a greater metal removal rate than with direct clamping.**
- **Concentricity $\pm 5 \mu\text{m}$ (system accuracy at $3 \times D$).**
- **Concentricity $\pm 2 \mu\text{m}$ (for reducing adapter).**
- **Can be used in all commercially available hydraulic chucks.**

Technical description

| | |
|---------------------------|------------------|
| Ø D | 20 mm |
| Clamping Ø D ₁ | 10 mm |
| External Ø | 20 mm |
| Product name attribute | Ø 20 mm |
| Concentricity system | 5 μm |
| Type of product | Reducing adapter |

