



## Slotted reducing adapter sealed, Ø 20 mm, Clamping range Ø D1: 12mm



### Order data

Order number	302165 12
GTIN	4060576159799
Item class	33T

### Description

#### Version:

Schunk GZB-S with seal.

Tight against coolant up to 80 bar.

Flexible length pre-setting possible through movable intermediate piece.

#### Sealed (rubber plug).

#### Application:

- **For drilling, reaming, milling, and tool sharpening.**
- **Very high flexibility due to reduction in clamping diameter.**
- **High torque guarantees a greater metal removal rate than with direct clamping.**
- **Concentricity  $\pm 5 \mu\text{m}$  (system accuracy at  $3 \times D$ ).**
- **Concentricity  $\pm 2 \mu\text{m}$  (for reducing adapter).**
- **Can be used in all commercially available hydraulic chucks.**

### Technical description

Clamping Ø D <sub>1</sub>	12 mm
Ø D	20 mm
External Ø	20 mm
Product name attribute	Ø 20 mm
Concentricity system	5 $\mu\text{m}$
Type of product	Reducing adapter

