



Slotted reducing adapter sealed, Ø 20 mm, Clamping range Ø D1: 16mm



Order data

Order number	302165 16
GTIN	4060576159751
Item class	33T

Description

Version:

Schunk GZB-S with seal.

Tight against coolant up to 80 bar.

Flexible length pre-setting possible through movable intermediate piece.

Sealed (rubber plug).

Application:

- **For drilling, reaming, milling, and tool sharpening.**
- **Very high flexibility due to reduction in clamping diameter.**
- **High torque guarantees a greater metal removal rate than with direct clamping.**
- **Concentricity $\pm 5 \mu\text{m}$ (system accuracy at $3 \times D$).**
- **Concentricity $\pm 2 \mu\text{m}$ (for reducing adapter).**
- **Can be used in all commercially available hydraulic chucks.**

Technical description

Ø D	20 mm
Clamping Ø D ₁	16 mm
External Ø	20 mm
Product name attribute	Ø 20 mm
Concentricity system	5 μm
Type of product	Reducing adapter

