

**Aluminium Oxide (A) finishing belt KK711T, 8×300 mm, Grit: 320****Order data**

Order number	558007 320
GTIN	4018875753545
Item class	56V

Description**Version:**

Universal finishing belt with **Aluminium Oxide(A)**. The grinding medium underlay is optimally designed to the grit and type of finishing belt.

40 grit - X-fabric (robust). 60 to 180 grit - T-fabric (robust-flexible) with **special flexibility**. Ideal for use on hand-held grinding machines.

Application:

For universal use on all popular materials: **steel**, non-ferrous metals, cast iron, **aluminium alloys**, **wood**.

Note:

Other grit sizes, qualities, and dimensions are available on request in line with the manufacturer's minimum order quantities. Unless specified otherwise on the order, belts will be supplied with standard joints. See No. 568526ff for spare finishing belts for burnishing machines.

Technical description

Grit	320
Series	KK711T
Grinding media	Standard aluminium oxide (A)

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Linishing belt width	8 mm
Linishing belt length	300 mm
Product name attribute	8×300 mm
Type of product	Linishing belt

User data

	Suitability	V _c	ISO code
Alu Mg	suitable	35-40 m/s	
Steel < 900 N/mm ²	suitable	32-38 m/s	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	20-25 m/s	P
Steel < 55 HRC	suitable only under restricted conditions	32-38 m/s	H
INOX	suitable only under restricted conditions	18-30 m/s	
Ti	suitable only under restricted conditions	10-20 m/s	
GG(G)	suitable only under restricted conditions	30-45 m/s	K
CuZn	suitable	35-45 m/s	N
Plastic, GRP	suitable	10-30 m/s	
Wood	suitable	23-26 m/s	
dry	suitable		