

**TESA**

Digital caliper SET TWIN-CAL IP67 with rod type depth gauge, measurement range 150 mm, Number of digital calipers: 150



Order data

Order number	405521 150
GTIN	4067263132738
Item class	45A

Description

Version:

- **Perfect guidance of the slide on the rail for easy and even smooth running.**
- **Sturdy design for long life and long-term stability of results.**
- **High protection category against dust and liquids.**
- **Easy to read with large, sharp-contrast round scale.**
- **Long battery life avoids frequent changing of batteries.**

Application:

External, internal, step and depth measurements.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

Technical description

IP Index of Protection	IP 67
Battery type	Button cell
Solar cells	no
Digit height LCD display	11 mm
Scale divisions	0.01 mm
Auto switch-off	yes

Automatic stand-by circuit.	yes
Number of batteries contained	1
Measuring range	0 - 150 mm
Working time	12000 hours
Reversible reading	mm / inch
Error limit	0.03 mm
Jaw length	40 mm
Scale divisions	0.0005 in
Depth gauge	round
Calibration	A1
Depth gauge available	yes
Power supply	Battery-powered
Interface	TESA Link Connector TLC
Interface	TESA Link Connector TLC
Interface	USB interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Accessories

Digital caliperTWIN-CAL IP67 with rod type depth gauge
Measuring range 150 mm

412785 150