



## DFG manual force gauge, Measuring range: 100N



### Order data

Order number	479025 100
GTIN	2050002070745
Item class	47F

### Description

#### Version:

Universal force gauge with colour display for precisely measuring tensile and compressive forces. Sturdy die-cast housing.

- **Displays the current force value and peak value.**
- **Programmable function keys.**
- **Monitoring of tolerance limits with visual and acoustic display.**
- **Memory for storing measurements.**
- **Statistical evaluation of saved values.**
- **Interface for exporting data.**
- **Display can be switched between N, gf, kgf, lbf, ozf.**

#### Supplied with:

Carrying case, charging plug with USB connecting cable, accessories (pressure pad, hook, tip, fin, V-slot, extension).

#### Optional extras:

Manual test stands No. 479029.

### Technical description

Height	42 mm
--------	-------

Width	84 mm
Measuring range	10 - 90 N
Accuracy	0.2 %
Length	191 mm
Resolution	0.02 N
Measured value memory	50
Power supply	Rechargeable battery-powered
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Type of product	Draw bar pulling force gauge