



DFG manual force gauge, Measuring range: 2500N



Order data

Order number	479025 2500
GTIN	2050002070783
Item class	47F

Description

Version:

Universal force gauge with colour display for precisely measuring tensile and compressive forces. Sturdy die-cast housing.

- **Displays the current force value and peak value.**
- **Programmable function keys.**
- **Monitoring of tolerance limits with visual and acoustic display.**
- **Memory for storing measurements.**
- **Statistical evaluation of saved values.**
- **Interface for exporting data.**
- **Display can be switched between N, gf, kgf, lbf, ozf.**

Supplied with:

Carrying case, charging plug with USB connecting cable, accessories (pressure pad, hook, tip, fin, V-slot, extension).

Optional extras:

Manual test stands No. 479029.

Technical description

Accuracy	0.2 %
----------	-------

Resolution	0.5 N
Height	42 mm
Width	84 mm
Length	191 mm
Measuring range	250 - 2250 N
Measured value memory	50
Power supply	Rechargeable battery-powered
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Type of product	Draw bar pulling force gauge