HOLEX

Metal band saw blade 27×3660, TPI: 6/10

Order data

Order number	173755 6/10
GTIN	4045197275714
Item class	12S

Description

Version:
HOLEX – Production band saw blade with high cutting performance.
Application:
Variable pitch teeth 0° – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).
Variable pitch teeth 10° – general purpose for a wide range of cross-sections (for solid material from 50 mm).
Regular pitch teeth 0° – for small to medium cross-sections up to maximum 70 mm engagement length.
Regular pitch teeth 10° – for large cross-sections from 50 mm engagement.
Note:
Running in a new blade: See GARANT machining handbook No. 110010 and information page.

Technical description

Width	27 mm
Thickness	0.9 mm

Length	3660 mm
Tooth type	combi
Rake	0 °
Tool material	HSS Co 8
Type of product	Metal band saw blade