



## Metal band saw blade 27×3660, TPI: 5/6H



### Order data

Order number	173755 5/6H
GTIN	4045197275677
Item class	12S

### Description

#### Version:

**HOLEX – Production band saw blade** with high cutting performance.

#### Application:

**Variable pitch teeth 0°** – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

**Variable pitch teeth 10° – general purpose** for a wide range of cross-sections (for solid material from 50 mm).

**Regular pitch teeth 0°** – for small to medium cross-sections up to maximum 70 mm engagement length.

**Regular pitch teeth 10°** – for large cross-sections from 50 mm engagement.

#### Note:

**Running in a new blade:** See GARANT machining handbook No. 110010 and information page.

### Technical description

Thickness	0.9 mm
Length	3660 mm

Width	27 mm
Tooth type	combi
Rake	10°
Tool material	HSS Co 8
Type of product	Metal band saw blade