



## Metal band saw blade 34×5000, TPI: 3/4H



### Order data

Order number	173864 3/4H
GTIN	2050001710161
Item class	16F

### Description

#### Version:

**RÖNTGEN – bi-alpha-cobalt: High-performance bi-metal band saw blade** with high chrome content **spring steel backing** and cobalt alloyed (M42) HSS tooth tips (67–69HRC). **Extreme tooth tip hardness, flexible backing.**

#### Application:

**Variable pitch teeth 0°** – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

**Variable pitch teeth 10° – general purpose** for a wide range of cross-sections (for solid material from 50 mm).

**Regular pitch teeth 0°** – for small to medium cross-sections up to maximum 70 mm engagement length.

**Regular pitch teeth 10°** – for large cross-sections from 50 mm engagement.

#### Note:

**Running in a new blade:** See GARANT machining handbook No. 110010 and information page.

### Technical description

Length	5000 mm
--------	---------

Thickness	1.1 mm
Width	34 mm
Rake	10°
Tooth type	combi
Tool material	HSS Co 8
Type of product	Metal band saw blade