

Garant
Adjustable hand reamer, Ø DC: 31,5mm

Order data

Order number	160600 31,5
GTIN	4045197250957
Item class	110

Description
Version:

Large adjustment range. Fine adjustment using ring gauges or micrometers.
Tools with taper lead; the flutes are relieved and cylindrically ground.

Technical description

Adjustment range Ø	31.5 - 37 mm
Nominal Ø D _c	31.5 mm
Shank square □	18 mm
Flute length L _c	98 mm
Overall length L	280 mm
Coating	uncoated
Tool material	HSS
Standard	Manufacturer's standard
Application for type of drilling	for through holes
Colour ring	without
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
--	-------------	----------------	----------

Aluminium (short chipping)	suitable
Steel < 500 N/mm ²	suitable
Steel < 750 N/mm ²	suitable
Steel < 900 N/mm ²	suitable only under restricted conditions
Oil	suitable
dry	suitable only under restricted conditions