



Pneumatic small angle grinder, Type: 52294



Order data

Order number	079325 52294
GTIN	616026522947
Item class	03R

Description

Version:

Small angle grinder with powerful pneumatic motor, maximum speed 20,000 rpm. **Collet Ø 6 mm**. For use as an angle miller or with backing disc No. 554090. 7° angle head, direct drive.

Supplied with:

Including the necessary coupling adaptors.

Note:

The 3M Roloc® small grinding system Ø 55 / 75 mm can be found under No. 554005 ff.

Technical description

maximum disc Ø	75 mm
maximum air consumption	1050 l/min
maximum speed	20000 min ⁻¹
recommended hose size (internal Ø)	10 mm
Operating noise	79 dB(A)
maximum vibration to EN	1.3 m/s ²

Weight	1 kg
Output power	522 W
Minimum disc Ø	50 mm
Manufacturer's designation	52294
Compressed air connection	1/4 in
Connection thread	NPT
Type of product	Angle grinder

Accessories

Grinding disc984F Grit 60	554006 60
Combidisc® grinding disc(SiC) Grit 120	554024 120
Grinding disc984F Grit 36	554006 36
Grinding disc237AA Grit 280	554008 280
Grinding disc(ZA) Grit 120	554018 120
Grinding disc237AA Grit 180	554008 180
Combidisc® grinding discDiamond Grit 220	554033 220
Grinding disc(CER) Grit 80	554012 80
Grinding disc984F Grit 36	554005 36
Grinding disc(ZA) Grit 120	554019 120
Combidisc® grinding disc(SiC) Grit 120	554023 120
Grinding disc984F Grit 80	554005 80
Grinding disc(ZA) Grit 50	554018 50
Grinding disc787C Grit 36	554016 36
Grinding disc984F Grit 80	554006 80
Grinding disc237AA Grit 280	554009 280
Grinding disc787C Grit 80	554014 80
Grinding disc787C Grit 60	554016 60
Combidisc® grinding disc(SiC) Grit 80	554023 80

Grinding disc237AA Grit 400	554009 400
Grinding disc237AA Grit 600	554008 600
Grinding disc(ZA) Grit 60	554018 60
Grinding disc(CER) Grit 60	554013 60
Grinding disc(ZA) Grit 36	554018 36
Grinding disc(ZA) Grit 80	554018 80
Combidisc® grinding disc(SiC) Grit 60	554024 60
Grinding disc(ZA) Grit 60	554019 60
Grinding disc(ZA) Grit 80	554019 80
Grinding disc787C Grit 120	554016 120
Combidisc® grinding disc(SiC) Grit 60	554023 60
Grinding disc237AA Grit 600	554009 600
Grinding disc(CER) Grit 36	554013 36
Combidisc® grinding discDiamond Grit 60	554033 60
Combidisc® grinding disc(SiC) Grit 36	554023 36
Grinding disc(ZA) Grit 36	554019 36
Grinding disc237AA Grit 120	554009 120
Combidisc® grinding disc(SiC) Grit 80	554024 80
Grinding disc787C Grit 80	554016 80
Grinding disc984F Grit 60	554005 60
Grinding disc787C Grit 36	554014 36
Grinding disc(CER) Grit 120	554013 120
Grinding disc237AA Grit 120	554008 120
Combidisc® grinding discDiamond Grit 120	554033 120
Combidisc® grinding disc(SiC) Grit 36	554024 36
Grinding disc(CER) Grit 60	554012 60
Grinding disc787C Grit 60	554014 60
Grinding disc(CER) Grit 80	554013 80
Grinding disc(CER) Grit 36	554012 36

Grinding disc237AA Grit 180	554009 180
Grinding disc237AA Grit 400	554008 400
Grinding disc(CER) Grit 120	554012 120
Grinding disc(ZA) Grit 50	554019 50
Grinding disc787C Grit 120	554014 120