



## Pneumatic die grinder, Type: 48325



### Order data

Order number	079443 48325
GTIN	616026483255
Item class	03R

### Description

#### Version:

#### **Dynabrade – pneumatic straight die grinder.**

Versatile, smooth running straight die grinders of robust and ergonomic design, with soft grip.

**Compact** 300 Watt straight die grinder, without gears, with a maximum speed of **25,000 rpm.**

Speed monitoring for constant speed under load. The upstream filter extends the working life of the tool.

#### **Supplied with:**

Including the necessary coupling adaptors.

### Technical description

Weight	0.41 kg
maximum speed	25000 min <sup>-1</sup>
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Length	202 mm
maximum air consumption	648 l/min
Operating noise	79 dB(A)
Collet Ø	6 mm

Output power	298 W
Manufacturer's designation	48325
Compressed air connection	1/4 in
Connection thread	NPT
Type of product	Straight die grinder

---

## Accessories

Collet Type 01497	079449 01497
-------------------	--------------