



Pneumatic angle grinder, Type: G2588-180



Order data

Order number	079312 G2588-180
GTIN	7322590042783
Item class	03R

Description

Version:

Powerful angle grinder, whose operating speed under load scarcely dips when load is applied. The safety starter prevents accidental starting. Angle grinder with 1700 Watt output power, designed for heavy-duty use and constant high material removal rate. Ergonomic in use. **M14 mounting thread.**

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Manufacturer's designation	G2588-180-M14
maximum vibration to EN	7.1 m/s ²
Operating noise	90 dB(A)
maximum disc Ø	180 mm
Weight	2.4 kg
Output power	1700 W

maximum speed	8500 min ⁻¹
maximum air consumption	2160 l/min
recommended hose size (internal Ø)	16 mm
Compressed air connection	1/2 in
Connection thread	BSP
Type of product	Angle grinder