



Pneumatic die grinder, Type: 52669



Order data

Order number	079443 52669
GTIN	616026526693
Item class	03R

Description

Version:

Dynabrade – pneumatic straight die grinder.

Versatile, smooth running straight die grinders of robust and ergonomic design, with soft grip.

Powerful 750 Watt straight die grinder, without gears, with a maximum speed of **20,000 rpm.**

Patented speed monitoring for constant speed even under load.

Supplied with:

Including the necessary coupling adaptors.

Technical description

Collet Ø	6 mm
Length	221 mm
Manufacturer's designation	52669
maximum speed	20000 min ⁻¹
maximum air consumption	1254 l/min
Output power	744 W
maximum vibration to EN	< 2.5 m/s ²
Operating noise	79 dB(A)

Weight	1 kg
Compressed air connection	3/8 in
Connection thread	NPT
Type of product	Straight die grinder

Accessories

Collet Type 50016	079449 50016
-------------------	--------------