

Garant
Gripp top jaw pivoting, for type: 125

Order data

Order number	361129 125
GTIN	4045197809407
Item class	310

Description
Application:

For mounting grip inserts No. 361160 7 and 361238 – 361250. For compensation of non-parallel clamping faces. Gripp inserts can be screwed into a variety of hole patterns, for secure clamping of various geometries.

Suitable for:

5-axis vice set No. 361100 and clamping module No. 361105 – 361110.

Supplied with:

Fastening screws.

Note:

Mounting recommendation on **fixed clamping module**.

Matching counter jaw No. 361128.

Technical description

Jaw height h	40 mm
suitable for colour code	Xpent1-2
Jaw width b	125 mm
Jaw length l	78.5 mm
Length l ₁	40 mm
Swing angle	30 degrees

Type of product

Vice jaws