



## Rechargeable LED EX work light, Type: NOVA-EXR



### Order data

|              |                 |
|--------------|-----------------|
| Order number | 081462 NOVA-EXR |
| GTIN         | 5708997356180   |
| Item class   | 08C             |

### Description

**Version:**

Explosion-proof work lamp, tested to the applicable ATEX guideline.

Extremely bright illumination and very long working life.

Sturdy and robust cordless LED EX work light.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Standard:**

Zertifiziert für ATEX-Zone: **Gas** 1 und 2, **Staub** 21 und 22.

ATEX-Richtlinie Nr. 2014/34/EU, IEC und IECEx zugelassen und zertifiziert.

**Supplied with:**

Supplied with 5 m charging cable.

**Attention:**

Attention: German version. Order free UK adapter plug No. 08 1172\_GB

### Technical description

|  |         |
|--|---------|
| Number of rechargeable batteries contained | 1       |
| Battery capacity                           | 3.35 Ah |

|                              |                              |
|------------------------------|------------------------------|
| Power supply                 | Rechargeable battery-powered |
| Tool properties              | Suitable for EX areas        |
| Battery voltage              | 21.6 V                       |
| Illumination time stage 2    | 4 h                          |
| Illumination step 2          | 4000 lm                      |
| Type of rechargeable battery | Lithium-ion                  |
| Weight                       | 3900 g                       |
| Bulb                         | LED module                   |
| Colour temperature           | 6000 K                       |
| IP Index of Protection       | IP 65                        |
| Lamp replaceable             | no                           |
| CRI value                    | 80                           |
| ATEX zone                    | Zone 21                      |
| ATEX zone                    | Zone 1                       |
| Overall width                | 261 mm                       |
| Illumination time            | 2 h                          |
| Overall height               | 130 mm                       |
| Overall length               | 270 mm                       |
| Illumination                 | 2000 lm                      |
| Manufacturer's designation   | NOVA EX R                    |
| Type of product              | Work lamp                    |