

**Pneumatic straight die grinder G2414, collet Ø 6 mm short, Type: S085****Order data**

Order number	079447 S085
GTIN	7322590019860
Item class	03R

Description**Version:**

Powerful and robust smooth-running straight die grinders. The safety switch prevents accidental switching on. Application-optimised maximum speeds between **8500 and 25,000 rpm.**

Short design, length 215 mm.

Collet Ø 6mm.

Supplied with:

Including the necessary coupling adaptors.

Spare part:**Selected service kits:**

Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Manufacturer's designation	G2414 S085
recommended hose size (internal Ø)	13 mm
Weight	0.78 kg
Output power	500 W

Operating noise	70 dB(A)
maximum speed	8500 min ⁻¹
maximum vibration to EN	< 2.5 m/s ²
maximum air consumption	252 l/min
Compressed air connection	3/8 in
Connection thread	BSP
Type of product	Straight die grinder

Accessories

Collet for straight grinder Collet Ø 6 mm	079459 6
---	----------