

**Pneumatic straight die grinder G2414, collets Ø 6 mm short, Type: S085****Order data**

Order number	079447 S085
GTIN	7322590019860
Item class	03R

**Description****Version:**

**Powerful and robust smooth-running straight die grinders.** The safety switch prevents accidental switching on. Application-optimised maximum speeds between **8500 and 25,000 rpm.**

Short design, length 215 mm.

**Collet Ø 6mm.**

**Supplied with:**

Including the necessary coupling adaptors.

**Spare part:****Selected service kits:**

Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

**Technical description**

Manufacturer's designation	G2414 S085
recommended hose size (internal Ø)	13 mm
Weight	0.78 kg
Output power	500 W

Operating noise	70 dB(A)
maximum speed	8500 min <sup>-1</sup>
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
maximum air consumption	252 l/min
Compressed air connection	3/8 in
Connection thread	BSP
Type of product	Straight die grinder

---

## Accessories

Collet for straight grinder Collet Ø 6 mm	079459 6
---	----------