



Pneumatic straight die grinder, Type: ST100



Order data

Order number	079440 ST100
GTIN	2050001763006
Item class	03P

Description

Version:

ATA – Pneumatic straight die grinder **with 3 mm collets** for fine milling, grinding and engraving. **Integral pre-filter.** 40W straight die grinder with high operating comfort and a maximum speed of 100,000 rpm.

Application:

Use only oil-free compressed air. Do not add oil!

Technical description

Collet Ø	3 mm
maximum vibration to EN	< 2.5 m/s ²
Manufacturer's designation	ST100
Operating noise	62 dB(A)
Length	160 mm
Output power	40 W
maximum air consumption	170 l/min
maximum speed	100000 min ⁻¹
Weight	0.24 kg
Compressed air connection	1/4 in
Connection thread	BSP

Type of product

Straight die grinder