



Pneumatic straight die grinder G2414, collets \varnothing 6 mm short, Type: S150



Order data

Order number	079447 S150
GTIN	7322590019846
Item class	03R

Description

Version:

Powerful and robust smooth-running straight die grinders. The safety switch prevents accidental switching on. Application-optimised maximum speeds between **8500 and 25,000 rpm.**

Short design, length 215 mm.

Collet \varnothing 6mm.

Supplied with:

Including the necessary coupling adaptors.

Spare part:**Selected service kits:**

Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Manufacturer's designation	G2414 S150
Weight	0.78 kg
maximum vibration to EN	2.5 m/s ²
Operating noise	76 dB(A)

Output power	850 W
maximum air consumption	432 l/min
maximum speed	15000 min ⁻¹
recommended hose size (internal Ø)	13 mm
Compressed air connection	3/8 in
Connection thread	BSP
Type of product	Straight die grinder

Accessories

Collet for straight grinder Collet Ø 6 mm	079459 6
---	----------