



Pneumatic die grinder, Type: 51813



Order data

Order number	079441 51813
GTIN	616026518131
Item class	03R

Description

Version:

Dynabrade – pneumatic straight die grinder.

Versatile, smooth running straight die grinders of robust and ergonomic design, with soft grip. Turbine-driven small straight die grinder with a **maximum speed of 100,000 rpm**. Equipped with high-quality high-speed bearings.

Application:

Use only oil-free compressed air. Do not add oil!

Supplied with:

Including the necessary coupling adaptors.

Technical description

Weight	0.4 kg
maximum vibration to EN	< 2.5 m/s ²
Length	135 mm
maximum speed	100000 min ⁻¹
maximum air consumption	170 l/min
Operating noise	81 dB(A)
Output power	75 W
Collet Ø	3 mm

Compressed air connection	1/4 in
Connection thread	NPT
Type of product	Straight die grinder