



## Pneumatic straight die grinder collet Ø 6 mm, Type: G2412



### Order data

Order number	079452 G2412
GTIN	7322590010058
Item class	03R

### Description

#### Version:

**Pneumatic straight die grinder.** Sturdy and smooth-running. The safety switch prevents accidental switching on.

**Collet Ø 6 mm.** Short version, maximum speed **20,000 rpm**.

#### Supplied with:

Including the necessary coupling adaptors.

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

Length	180 mm
maximum speed	20000 min <sup>-1</sup>
maximum air consumption	618 l/min
Weight	0.5 kg
Output power	350 W
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Operating noise	79 dB(A)

Manufacturer's designation	G2412-1
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Straight die grinder

---

## Accessories

Collet for straight grinder Collet Ø 6 mm	079459 6
---	----------