



## Pneumatic straight die grinder G2414, collets $\varnothing$ 6 mm short, Type: S200



### Order data

Order number	079447 S200
GTIN	7322590013615
Item class	03R

### Description

#### Version:

**Powerful and robust smooth-running straight die grinders.** The safety switch prevents accidental switching on. Application-optimised maximum speeds between **8500 and 25,000 rpm.**

Short design, length 215 mm.

**Collet  $\varnothing$  6mm.**

#### Supplied with:

Including the necessary coupling adaptors.

#### Spare part:

#### Selected service kits:

Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

maximum air consumption	540 l/min
maximum speed	20000 min <sup>-1</sup>
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Manufacturer's designation	G2414 S200

Output power	900 W
recommended hose size (internal Ø)	13 mm
Operating noise	81 dB(A)
Weight	0.78 kg
Compressed air connection	3/8 in
Connection thread	BSP
Type of product	Straight die grinder

---

## Accessories

Collet for straight grinder Collet Ø 6 mm	079459 6
---	----------