



Pneumatic die grinder, Type: 51701



Order data

Order number	079441 51701
GTIN	616026517011
Item class	03R

Description

Version:

Dynabrade – pneumatic straight die grinder.

Versatile, smooth running straight die grinders of robust and ergonomic design, with soft grip.

Turbine-driven small straight grinder, without gears, with a maximum speed of **60,000 rpm**.

Ceramic bearings, pneumatic drive with **patented speed monitoring** for constant speed under load.

Application:

Use only oil-free compressed air. Do not add oil!

Supplied with:

Including the necessary coupling adaptors.

Technical description

Operating noise	66 dB(A)
Length	132 mm
maximum air consumption	228 l/min
maximum speed	60000 min ⁻¹
Weight	0.4 kg
Output power	75 W
Manufacturer's designation	51701
Collet Ø	3 mm

maximum vibration to EN	< 2.5 m/s ²
Compressed air connection	1/4 in
Connection thread	NPT
Type of product	Straight die grinder

Accessories

Collet Type 51673	079449 51673
-------------------	--------------