



## Pneumatic pistol-grip angle grinder, Type: G2302



### Order data

|              |               |
|--------------|---------------|
| Order number | 079311 G2302  |
| GTIN         | 7322590019815 |
| Item class   | 03R           |

### Description

#### Version:

**Small pistol-grip angle grinder** with two Roloc® mini-grinding discs Ø 50/75 mm. Speed can be precisely adjusted using the starter pushbutton. Rubber-coated handle is comfortable to use.

#### Function:

IP20: No protection against penetration by foreign bodies with Ø < 12 mm, however touching should be avoided, and no protection against water.

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

#### Note:

The 3M Roloc® small grinding system Ø 55 / 75 mm can be found under No. 554005 ff.

Output power: 175 W

maximum speed: 17000 min<sup>-1</sup>

maximum air consumption: 534 l/min

Connection thread: BSP

Compressed air connection: 1/4 in

maximum vibration to EN: < 2.5 m/s<sup>2</sup>

### Technical description

|                                    |                         |
|------------------------------------|-------------------------|
| Manufacturer's designation         | G2302                   |
| Weight                             | 0.6 kg                  |
| maximum disc Ø                     | 75 mm                   |
| recommended hose size (internal Ø) | 10 mm                   |
| Minimum disc Ø                     | 50 mm                   |
| Output power                       | 175 W                   |
| Operating noise                    | 81 dB(A)                |
| maximum vibration to EN            | < 2.5 m/s <sup>2</sup>  |
| maximum air consumption            | 534 l/min               |
| maximum speed                      | 17000 min <sup>-1</sup> |
| Compressed air connection          | 1/4 in                  |
| Connection thread                  | BSP                     |
| Type of product                    | Angle grinder           |

## Accessories

|   |            |
|---|------------|
| Grinding disc 984F Grit 80                | 554006 80  |
| Grinding disc 237AA Grit 400              | 554009 400 |
| Grinding disc 787C Grit 60                | 554016 60  |
| Grinding disc (CER) Grit 36               | 554013 36  |
| Grinding disc (ZA) Grit 36                | 554018 36  |
| Grinding disc 984F Grit 60                | 554006 60  |
| Grinding disc (CER) Grit 120              | 554013 120 |
| Grinding disc 787C Grit 80                | 554016 80  |
| Combidisc® grinding disc Diamond Grit 120 | 554033 120 |
| Combidisc® grinding disc (SiC) Grit 120   | 554023 120 |
| Grinding disc (ZA) Grit 60                | 554019 60  |
| Grinding disc 787C Grit 60                | 554014 60  |

|   |            |
|---|------------|
| Grinding disc 237AA Grit 180              | 554008 180 |
| Grinding disc (ZA) Grit 50                | 554018 50  |
| Grinding disc (ZA) Grit 80                | 554018 80  |
| Grinding disc 787C Grit 120               | 554014 120 |
| Grinding disc 237AA Grit 600              | 554008 600 |
| Grinding disc 237AA Grit 280              | 554009 280 |
| Grinding disc 984F Grit 36                | 554006 36  |
| Combidisc® grinding disc Diamond Grit 220 | 554033 220 |
| Grinding disc 787C Grit 80                | 554014 80  |
| Grinding disc 787C Grit 36                | 554016 36  |
| Grinding disc (ZA) Grit 120               | 554019 120 |
| Grinding disc 237AA Grit 600              | 554009 600 |
| Combidisc® grinding disc (SiC) Grit 36    | 554024 36  |
| Grinding disc 984F Grit 80                | 554005 80  |
| Grinding disc (ZA) Grit 36                | 554019 36  |
| Grinding disc (ZA) Grit 60                | 554018 60  |
| Grinding disc (CER) Grit 80               | 554013 80  |
| Grinding disc (CER) Grit 120              | 554012 120 |
| Grinding disc 237AA Grit 120              | 554009 120 |
| Combidisc® grinding disc (SiC) Grit 36    | 554023 36  |
| Combidisc® grinding disc (SiC) Grit 60    | 554024 60  |
| Grinding disc (CER) Grit 60               | 554013 60  |
| Grinding disc (ZA) Grit 80                | 554019 80  |
| Grinding disc (ZA) Grit 50                | 554019 50  |
| Combidisc® grinding disc (SiC) Grit 80    | 554024 80  |
| Combidisc® grinding disc (SiC) Grit 120   | 554024 120 |
| Grinding disc (CER) Grit 36               | 554012 36  |
| Combidisc® grinding disc (SiC) Grit 60    | 554023 60  |
| Grinding disc 237AA Grit 180              | 554009 180 |

|  |            |
|--|------------|
| Combidisc® grinding disc (SiC) Grit 80   | 554023 80  |
| Grinding disc 787C Grit 36               | 554014 36  |
| Grinding disc 984F Grit 36               | 554005 36  |
| Grinding disc 787C Grit 120              | 554016 120 |
| Combidisc® grinding disc Diamond Grit 60 | 554033 60  |
| Grinding disc 984F Grit 60               | 554005 60  |
| Grinding disc 237AA Grit 400             | 554008 400 |
| Grinding disc 237AA Grit 280             | 554008 280 |
| Grinding disc (CER) Grit 60              | 554012 60  |
| Grinding disc (ZA) Grit 120              | 554018 120 |
| Grinding disc 237AA Grit 120             | 554008 120 |
| Grinding disc (CER) Grit 80              | 554012 80  |