



Pneumatic pistol-grip angle grinder, Type: G2302



Order data

Order number	079311 G2302
GTIN	7322590019815
Item class	03R

Description

Version:

Small pistol-grip angle grinder with two Roloc® mini-grinding discs Ø 50/75 mm. Speed can be precisely adjusted using the starter pushbutton. Rubber-coated handle is comfortable to use.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Note:

The 3M Roloc® small grinding system Ø 55 / 75 mm can be found under No. 554005 ff.

Technical description

Manufacturer's designation	G2302
Weight	0.6 kg
maximum disc Ø	75 mm
recommended hose size (internal Ø)	10 mm
Minimum disc Ø	50 mm

Output power	175 W
Operating noise	81 dB(A)
maximum vibration to EN	< 2.5 m/s ²
maximum air consumption	534 l/min
maximum speed	17000 min ⁻¹
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Angle grinder

Accessories

Grinding disc984F Grit 80	554006 80
Grinding disc237AA Grit 400	554009 400
Grinding disc787C Grit 60	554016 60
Grinding disc(CER) Grit 36	554013 36
Grinding disc(ZA) Grit 36	554018 36
Grinding disc984F Grit 60	554006 60
Grinding disc(CER) Grit 120	554013 120
Grinding disc787C Grit 80	554016 80
Combidisc® grinding discDiamond Grit 120	554033 120
Combidisc® grinding disc(SiC) Grit 120	554023 120
Grinding disc(ZA) Grit 60	554019 60
Grinding disc787C Grit 60	554014 60
Grinding disc237AA Grit 180	554008 180
Grinding disc(ZA) Grit 50	554018 50
Grinding disc(ZA) Grit 80	554018 80
Grinding disc787C Grit 120	554014 120
Grinding disc237AA Grit 600	554008 600
Grinding disc237AA Grit 280	554009 280

Grinding disc984F Grit 36	554006 36
Combidisc® grinding discDiamond Grit 220	554033 220
Grinding disc787C Grit 80	554014 80
Grinding disc787C Grit 36	554016 36
Grinding disc(ZA) Grit 120	554019 120
Grinding disc237AA Grit 600	554009 600
Combidisc® grinding disc(SiC) Grit 36	554024 36
Grinding disc984F Grit 80	554005 80
Grinding disc(ZA) Grit 36	554019 36
Grinding disc(ZA) Grit 60	554018 60
Grinding disc(CER) Grit 80	554013 80
Grinding disc(CER) Grit 120	554012 120
Grinding disc237AA Grit 120	554009 120
Combidisc® grinding disc(SiC) Grit 36	554023 36
Combidisc® grinding disc(SiC) Grit 60	554024 60
Grinding disc(CER) Grit 60	554013 60
Grinding disc(ZA) Grit 80	554019 80
Grinding disc(ZA) Grit 50	554019 50
Combidisc® grinding disc(SiC) Grit 80	554024 80
Combidisc® grinding disc(SiC) Grit 120	554024 120
Grinding disc(CER) Grit 36	554012 36
Combidisc® grinding disc(SiC) Grit 60	554023 60
Grinding disc237AA Grit 180	554009 180
Combidisc® grinding disc(SiC) Grit 80	554023 80
Grinding disc787C Grit 36	554014 36
Grinding disc984F Grit 36	554005 36
Grinding disc787C Grit 120	554016 120
Combidisc® grinding discDiamond Grit 60	554033 60
Grinding disc984F Grit 60	554005 60

Grinding disc237AA Grit 400	554008 400
Grinding disc237AA Grit 280	554008 280
Grinding disc(CER) Grit 60	554012 60
Grinding disc(ZA) Grit 120	554018 120
Grinding disc237AA Grit 120	554008 120
Grinding disc(CER) Grit 80	554012 80