



## Pneumatic die grinder collet Ø 6 mm, Type: G2422



### Order data

Order number	079452 G2422
GTIN	7322590011086
Item class	03R

### Description

**Version:**

**Pneumatic straight grinder.** Sturdy and smooth-running. The safety switch prevents accidental switching on.

**Collet Ø 6 mm.** Long version with slim shank, ideal for holes, maximum speed **20,000 rpm.**

**Supplied with:**

Including the necessary coupling adaptors.

**Spare part:**

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

maximum speed	20000 min <sup>-1</sup>
maximum air consumption	618 l/min
Weight	0.7 kg
Manufacturer's designation	G2422-1
Length	277 mm
maximum vibration to EN	3.4 m/s <sup>2</sup>
Output power	350 W

Operating noise	77 dB(A)
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Straight die grinder

---

## Accessories

Collet for straight grinder Collet Ø 6 mm	079459 6
-------------------------------------------	----------