



Pneumatic straight die grinder collet Ø 6 mm, Type: G2422



Order data

Order number	079452 G2422
GTIN	7322590011086
Item class	03R

Description

Version:

Pneumatic straight die grinder. Sturdy and smooth-running. The safety switch prevents accidental switching on.

Collet Ø 6 mm. Long version with slim shank, ideal for holes, maximum speed **20,000 rpm.**

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

maximum speed	20000 min ⁻¹
maximum air consumption	618 l/min
Weight	0.7 kg
Manufacturer's designation	G2422-1
Length	277 mm
maximum vibration to EN	3.4 m/s ²
Output power	350 W

Operating noise	77 dB(A)
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Straight die grinder

Accessories

Collet for straight grinder Collet Ø 6 mm	079459 6
---	----------