



Precision cylinder lock without lock barrel, Body Ø: 45mm



Order data

Order number	085816 45
GTIN	2050000971969
Item class	08Q

Description

Version:

Precision padlock, brass body nickel-plated, shackle made of hardened steel, chrome-plated, and double locked. With integrated lock barrel No. 950050 (not for No. 085816) for individual configuration / integration into your existing DOM locking system. Can be individually fitted using lock barrel No. 950050 to suit your requirements.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Note:

For individually configurable lock barrels see No. 950050 and No. 950072, **group 95 in the Workstations and Storage catalogue volume 3.**

Hoop \varnothing : 6 mm

Technical description

Type of locking	Cylinder lock
Hoop hardened	yes
Supplied without lock barrel	yes
Lock number range	HO 001 - 200 or locking system lock number

Material of the housing	Nickel-plated brass
Body Ø	45 mm
Material of the band	Steel
suitable for lock barrels	yes
Hoop Ø	6 mm
compatible with integrated locking systems	yes
Shackle, double lever mechanism	yes
Type of product	Padlock

Accessories

Lock barrel with 2 keys Lock number Ho (3-digit) 003	960000 003
Locking system barrel insert with 2 keys Hierarchical levels / maximum number of locks 1/100	960022 1/100
Lock barrel with 2 keys Lock number Ho (3-digit) 002	960000 002
Locking system barrel insert with 2 keys Hierarchical levels / maximum number of locks 3/300	960022 3/300
Lock barrel with 2 keys Lock number Ho (3-digit) 004	960000 004
Lock barrel with 2 keys Lock number Ho (3-digit) 005	960000 005
Locking system barrel insert with 2 keys Hierarchical levels / maximum number of locks 1/300	960022 1/300
Lock barrel with 2 keys Lock number Ho (3-digit) 001	960000 001
Locking system barrel insert with 2 keys Hierarchical levels / maximum number of locks 3/2000	960022 3/2000