


Garant**Die 6g, M: M1,2**

Order data

Order number	140300 M1,2
GTIN	4045197083029
Item class	11K

Description

Version:

Closed, pre-slit form. \geq **M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1 $\frac{3}{4}$ turns lead chamfer.** Tolerance zone 6h.

Technical description

Pitch	0.25 mm
Height	5 mm
External \varnothing	16 mm
Tolerance class	DIN 13 6h
Thread size	M1.2
Thread type	M
Flank angle	60 degrees
Tool material	HSS

Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		