



Pneumatic angle grinder, Type: G2408-115



Order data

Order number	079312 G2408-115
GTIN	7322590010065
Item class	03R

Description

Version:

Powerful angle grinder, whose operating speed under load scarcely dips when load is applied. The safety starter prevents accidental starting.

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Manufacturer's designation	G2408-115
maximum vibration to EN	8,1 m/s ²
maximum air consumption	786 l/min
maximum disc Ø	115 mm
Weight	0.9 kg

Output power	350 W
recommended hose size (internal Ø)	10 mm
maximum speed	12000 min ⁻¹
Operating noise	81 dB(A)
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Angle grinder