



Pneumatic straight die grinder G2424, collets \varnothing 6 mm long, Type: S085



Order data

Order number	079448 S085
GTIN	7322590019891
Item class	03R

Description

Version:

Powerful and robust smooth-running straight die grinders. The safety switch prevents accidental switching on. Application-optimised maximum speeds between **8500 and 25,000 rpm.**

With long, slim spindle, ideal for holes length 317 mm.

Collet \varnothing 6mm.

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits:

Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

maximum speed	8500 min ⁻¹
recommended hose size (internal \varnothing)	13 mm
Operating noise	70 dB(A)
Manufacturer's designation	G2424 S085

maximum vibration to EN	5.3 m/s ²
Output power	440 W
Weight	0.96 kg
maximum air consumption	252 l/min
Compressed air connection	3/8 in
Connection thread	BSP
Type of product	Straight die grinder

Accessories

Collet for straight grinder Collet Ø 6 mm	079459 6
---	----------