

HOLEX®
Die 6g, M: M12

Order data

Order number	140320 M12
GTIN	4045197083319
Item class	12K

Description
Version:

Closed, pre-slit form. **≥ M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1 ¾ turns lead chamfer.**

Thread type: M

Flank angle: 60 degrees

Tool material: HSS

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1.75 mm

External Ø: 38 mm

Height: 14 mm

Technical description

Height	14 mm
Pitch	1.75 mm
External Ø	38 mm

Tolerance class	DIN 13 6g
Thread size	12
Thread type	M
Flank angle	60 degrees
Tool material	HSS
Norm	EN 22568
Cutting direction	right-hand